



Overview

Presentation	This 6" wide, high capacity vertical cable manager for 2 and 4 Post open frame racks features a double-sided cable channel with multiple internal cable tie-off locations and smooth plastic fingers at 1U increments for organized patching applications.
Lead time	Usually in Stock

Main

Provided equipment	Doors Installation guide Mounting Hardware 3 x Midspan brackets
--------------------	--

Physical

Color	Black
Height	84.02 in (213.4 cm)
Width	5.98 in (15.2 cm)
Depth	25.98 in (66 cm)
Net Weight	65.92 lb(US) (29.9 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Conformance

Product Certifications	UL Listed
------------------------	-----------

Ordering and shipping details

GTIN	731304291572
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.97 in (30.4 cm)
Package 1 Width	90.04 in (228.7 cm)
Package 1 Length	32.52 in (82.6 cm)
Package 1 Weight	85.98 lb(US) (39 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------