

Product data sheet

Characteristics

9001SK1L32

PUSHBUTTON OPERATOR 30MM SK +OPTIONS

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Bezel material	Black plastic
Control button type	Standard push-button
Device short name	SK
Enclosure type	Dust and oil resistant weatherproof enclosure indoor/outdoor Corrosion resistance enclosure indoor/outdoor
Mounting diameter	1.18 in (30 mm)
Operator additional information	Full guard in plastic

Complementary

Cap/operator or lens colour	Without cap
Contacts type and composition	Without contact block
Control type	Illuminated push-button
Electrical connection	Screw clamp terminal
Light block supply	12 V AC full voltage 14 V AC full voltage
Marking	Unmarked
Mounting support	Panel
Operator position information	2 positions
Operator profile	1 projecting push-button
Shape	Round head
Type of operator	Momentary
Utilisation category	AC-15 DC-13

Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/4X/6/12/13
Product certifications	CE UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03

Ordering and shipping details

Category	21429 - 9001 SK,SKY
Discount Schedule	CS1
GTIN	00785901178392
Nbr. of units in pkg.	1
Package weight(Lbs)	0.4000000000000002
Returnability	N
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------
