



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided Equipment	All required connectors Battery recycling guide Installation guide Reusable packaging
--------------------	--

Physical

Color	Black
Depth	16.50 in (41.9 cm)
Height	3.27 in (8.3 cm)
Product Weight	23.85 lb(US) (10.82 kg)
Width	6.50 in (16.5 cm)

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...95 %

Batteries & Runtime

Battery Placement	Internal Battery
Battery blocks per string	4
Battery Slots Empty	0
Included Battery Modules	0
Device mounting	Enclosed battery cartridge
Battery Voltage	48V
Battery Type	Lead-Acid battery
RBC Quantity	1

Ordering and shipping details

Package weight(Lbs)	25.86 lb(US) (11.73 kg)
---------------------	-------------------------

Packing Units

Package 1 Height	7.48 in (19 cm)
Package 1 width	11.50 in (29.2 cm)
Package 1 Length	21.50 in (54.6 cm)
Number of Units in Package 3	24

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Take-back	Take-back program available