

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Bezel material	Chromium plated metal
Device short name	K
Enclosure type	Weatherproof enclosure dust and oil resistant in-door/outdoor
Mounting diameter	1.18 in (30 mm)

Complementary

Line Rated Current	10 A
Cap/operator or lens colour	Amber
Contact operation	Standard fingersafe
Contacts type and composition	1 NO + 3 NC
Control type	Illuminated push-button
Electrical connection	Screw clamp terminal
Light block supply	Via transformer 120 V AC 50/60 Hz Via transformer 110 V AC 50/60 Hz
Mounting support	Panel
Operator position information	4 positions
Operator profile	Standard knob
Operator profile	1 projecting push-button
Permissible voltage	<= 600 V
Shape	Round head
Type of operator	Maintained
Utilisation category	AC-15 DC-13

Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13
Product certifications	CE UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03

Ordering and shipping details

Category	21426 - 9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	00785901790815
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5
Returnability	N
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------