

Product availability: Non-Stock - Not normally stocked in distribution facility



### Main

|                                 |                                                              |
|---------------------------------|--------------------------------------------------------------|
| Bezel material                  | Chromium plated metal                                        |
| Control button type             | Key operated push-button                                     |
| Device short name               | K                                                            |
| Enclosure type                  | Dust and oil resistant weatherproof enclosure indoor/outdoor |
| Light source                    | Without                                                      |
| Mounting diameter               | 1.18 in (30 mm)                                              |
| Operator additional information | Full guard in metal                                          |

### Complementary

|                               |                                                                               |
|-------------------------------|-------------------------------------------------------------------------------|
| Contacts type and composition | Without contact block                                                         |
| Control type                  | Push-button                                                                   |
| Key number                    | E31                                                                           |
| Light block supply            | Without supply                                                                |
| Marking                       | Unmarked                                                                      |
| Mounting support              | Panel                                                                         |
| Operator position information | 3 positions                                                                   |
| Operator profile              | 1 projecting push-button                                                      |
| Shape                         | Round head                                                                    |
| Type of operator              | Extended position lockable test button with key withdrawal in locked position |
| Utilisation category          | AC-15<br>DC-13                                                                |

### Environment

|                           |                                                                   |
|---------------------------|-------------------------------------------------------------------|
| NEMA degree of protection | NEMA 1/2/3/3R/4/6/12/13                                           |
| Product certifications    | CE<br>UL listed file E42259 CCN NKCR<br>CSA LR24590 class 3211 03 |

### Ordering and shipping details

|                       |                               |
|-----------------------|-------------------------------|
| Category              | 21426 - 9001 K (NOT KA,KM,KX) |
| Discount Schedule     | CS1                           |
| GTIN                  | 00785901582175                |
| Nbr. of units in pkg. | 1                             |
| Package weight(Lbs)   | 0.5                           |
| Returnability         | N                             |
| Country of origin     | MX                            |

### Offer Sustainability

|                           |                                                                                                                                  |
|---------------------------|----------------------------------------------------------------------------------------------------------------------------------|
| California proposition 65 | WARNING: This product can expose you to chemicals including:                                                                     |
| ----- Substance 1         | Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. |
| ----- More information    | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>                                    |

Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|