

Product data sheet

Characteristics

D10S3

Operating mechanism, disconnect switch,
100A, 600 VAC, NEMA Size 3



Main

Range	D10S
Product	Disconnect Switch
Current Rating	100 A
Horsepower Rating	15 Hp 120 V AC 30 Hp 200/240 V AC 60 Hp 480 V AC 75 hp 600 V AC
Voltage Rating	600 V AC
Mounting Type	Door
NEMA Size	3
Service Entrance Rated	Not service entrance rated

Ordering and shipping details

Category	22642 - DISCONNECT SWITCHES - D10
Discount Schedule	T
GTIN	00785901118619
Nbr. of units in pkg.	1
Package weight(Lbs)	7.79 lb(US) (3.53 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	4.00 in (10.16 cm)
Package 1 width	11.00 in (27.94 cm)
Package 1 Length	16.80 in (42.672 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Not compliant
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.