

HMIVXL3PRT4KLV80

EcoStruxure Machine SCADA Expert for Line Management (3rd party PC Runtime License), 4000 Tags



Main

Range of Product	EcoStruxure Machine SCADA Expert
Product or Component Type	Software
User Language	Multi-language
Format	Sticker
Previous software version	V8.1 SP5

Complementary

Software Designation	Line management
Type of License	Design/operation (BT/RT)
Software Type	EcoStruxure machine SCADA Expert software
System requirements	> 2 GB HDD storage device, > 2 GB primary memory > 2 GB HDD storage device Windows 8.1, > 2 GB primary memory > 2 GB HDD storage device Windows 10, > 2 GB primary memory > 2 GB HDD storage device Windows Server 2008 R2, > 2 GB primary memory > 2 GB HDD storage device Windows Server 2012 R2, > 2 GB primary memory > 2 GB HDD storage device Windows Server 2016, > 2 GB primary memory - Microsoft internet explorer 11 - External audio and video files .NET Framework 3.5
Software Version	V20.0
Provided Equipment	User's documentation in electronic format
Document type	- Quick start-up guide - Technical reference manual - Training manual
Software Function	- Database connection - E-signature
Audio video coding standard	- MP3 - WAV - AVI - MOV - MP4 - MPEG

Ordering and shipping details

Category	22574 - MAGELIS BOX PC AND PANEL PC
Discount Schedule	MC2
GTIN	3606489502430
Nbr. of units in pkg.	1
Package weight(Lbs)	0.28 oz (8 g)
Returnability	No

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.04 in (0.1 cm)
Package 1 width	4.72 in (12 cm)
Package 1 Length	5.51 in (14 cm)