

# Product data sheet

## Characteristics

### KAXZ1S149

Cam switch operating head, Harmony K, Ø 22mm, metal, circular Ø 29mm, key operated 45°, special key



#### Main

Range of Product	Harmony Series K
Product or Component Type	Cam switch operating head
Component name	KAX
Product compatibility	Front mounting bodies 12 and 20 A Ø 22 mm hole
Cam switch head type	With bezel Ø 28.5 mm, metal
Type of operator	Key key other number
Rotary handle padlocking	Without
Presentation of legend	With mat black
Switching angle	45 °

#### Complementary

Mechanical durability	1000000 cycles
Net Weight	0.14 lb(US) (0.065 kg)
Compatibility code	KAX

#### Environment

Protective treatment	TC
Ambient Air Temperature for Operation	-13...131 °F (-25...55 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Shock resistance	30 gn IEC 68-2-27
Vibration resistance	5 gn 10...150 Hz)IEC 68-2-6
IP degree of protection	IP65 conforming to IEC 529 IP65 conforming to NF C 20-010

#### Ordering and shipping details

Category	21446-9003 K CAM SWITCHES
Discount Schedule	CS1
GTIN	3389110885866
Returnability	No
Country of origin	CZ

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.22 in (3.1 cm)
Package 1 Width	1.22 in (3.1 cm)
Package 1 Length	2.36 in (6.0 cm)
Package 1 Weight	2.40 oz (68.0 g)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#"> REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#"> EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#"> China RoHS Declaration</a>
RoHS exemption information	<a href="#"> Yes</a>

## Contractual warranty

Warranty	18 months
----------	-----------