



### Overview

|           |                  |
|-----------|------------------|
| Lead time | Usually in Stock |
|-----------|------------------|

### Physical

|                     |                       |
|---------------------|-----------------------|
| Height              | 0.55 in (1.4 cm)      |
| Width               | 4.92 in (12.5 cm)     |
| Depth               | 4.92 in (12.5 cm)     |
| Net Weight          | 0.31 lb(US) (0.14 kg) |
| Mounting preference | No preference         |
| Mounting Mode       | Not rack-mountable    |

### Conformance

|                        |                                                |
|------------------------|------------------------------------------------|
| Product Certifications | C-tick<br>CE<br>TAA compliance<br>VCCI Class A |
| Standards              | FCC Part 15 class A<br>ICES-003<br>UL 60950-1  |

### Environmental

|                                       |                                 |
|---------------------------------------|---------------------------------|
| Ambient Air Temperature for Operation | 32...122 °F (0...50 °C)         |
| Operating altitude                    | 0...10000 ft                    |
| Relative Humidity                     | 5...95 %                        |
| Ambient Air Temperature for Storage   | 14...140 °F (-10...60 °C)       |
| Storage altitude                      | 0...10000 ft (0.00...3048.00 m) |
| Storage Relative Humidity             | 5...95 %                        |

### Ordering and shipping details

|                     |                       |
|---------------------|-----------------------|
| GTIN                | 731304286660          |
| Package weight(Lbs) | 0.40 lb(US) (0.18 kg) |

### Packing Units

|                  |                   |
|------------------|-------------------|
| Package 1 Height | 1.65 in (4.2 cm)  |
| Package 1 width  | 4.92 in (12.5 cm) |
| Package 1 Length | 5.08 in (12.9 cm) |
| SCC14            | 10731304286667    |

Offer Sustainability

|                           |                                                                                                                                                                                                                                                    |
|---------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| EU RoHS Directive         | Compliant <a href="#">EU RoHS Declaration</a>                                                                                                                                                                                                      |
| WEEE                      | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.                                                                                                                       |

Contractual warranty

|          |                           |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|