

Product data sheet

Characteristics

9001KA12

PUSH BUTTON CONTACT 600VAC 10A 30MM T-K

Product availability: Stock - Normally stocked in distribution facility

Main

Device short name	K
Mounting diameter	1.18 in (30 mm)

Complementary

Line Rated Current	10 A
Contact operation	Standard without fingersafe
Contacts type and composition	1 NO
Electrical connection	Quick connect terminals
Permissible voltage	<= 600 V

Environment

Product certifications	CE UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03
------------------------	---

Ordering and shipping details

Category	21434 - 9001 KA CONTACT BLOCKS
Discount Schedule	CS1
GTIN	00785901716839
Nbr. of units in pkg.	1
Package weight(Lbs)	4.0000000000000001E-2
Returnability	Y
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0921 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------