

Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

General

Provided Equipment	User Manual
--------------------	-------------

Physical

Color	Gray
Depth	16.30 in (41.4 cm)
Height	6.42 in (16.3 cm)
Product Weight	37.48 lb(US) (17 kg)
Width	8.50 in (21.6 cm)

Conformance

Product Certifications	CE UL Listed
------------------------	-----------------

Environmental

Ambient Air Temperature for Operation	64...82 °F (18...28 °C)
Ambient Air Temperature for Storage	32...104 °F (0...40 °C)
Storage Relative Humidity	0...60 %

Batteries & Runtime

Battery Slots Empty	0
Included Battery Modules	0
Battery manufacturer	Samsung
Battery Type	Li-Ion (Lithium Ion)
Battery power in VAh	0 VAh

Ordering and shipping details

Package weight(Lbs)	40.48 lb(US) (18.36 kg)
---------------------	-------------------------

Packing Units

Package 1 Height	9.41 in (23.9 cm)
Package 1 width	11.50 in (29.2 cm)
Package 1 Length	19.29 in (49 cm)

Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------