



## Overview

Presentation	Network appliances enabling remote and local access control for your NetShelter SX enclosures.
Lead time	Usually in Stock



## Main

Number of rack unit	1U
Communication port protocol	A-Link SNMP
Provided Equipment	Cable ties Door sensor Installation guide Lock handles Proximity reader Rack Mounting brackets User Manual

## Physical

Height	1.73 in (4.4 cm)
Width	17.01 in (43.2 cm)
Depth	2.32 in (5.9 cm)
Net Weight	2.80 lb(US) (1.27 kg)
Mounting preference	No preference
Mounting Mode	Rack-mounted

## Environmental

Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...149 °F (-15...65 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...95 %

## Ordering and shipping details

GTIN	3606481978028
Package weight(Lbs)	5.40 lb(US) (2.45 kg)

## Packing Units

Package 1 Height	7.64 in (19.4 cm)
Package 1 width	35.59 in (90.4 cm)
Package 1 Length	20.83 in (52.9 cm)

## Offer Sustainability

EU RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS  
Declaration