



Overview

Presentation	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
Lead time	Usually Ships within 3 Weeks

Main

Main Input Voltage	230 V
Main Output Voltage	240 V
Plug standard	IEC 60309
Provided Equipment	Installation guide

Physical

Color	Gray
Height	5.00 in (12.7 cm)
Width	17.48 in (44.4 cm)
Depth	15.98 in (40.6 cm)
Net Weight	9.41 lb(US) (4.27 kg)

Input

Input Frequency	60 Hz
Acceptable Input Voltage	200...240 V
Max line current	20 A

Output

Maximum Total Current Draw per Phase	20 A
Number of power socket outlets	1 IEC 309

Conformance

Product Certifications	UL Listed
------------------------	-----------

Ordering and shipping details

GTIN	731304265382
Package weight(Lbs)	10.63 lb(US) (4.82 kg)

Packing Units

Package 1 Height	5.00 in (12.7 cm)
Package 1 width	17.48 in (44.4 cm)
Package 1 Length	15.98 in (40.6 cm)

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------