



Overview

Lead time	Usually Ships within 2 Weeks
-----------	------------------------------

General

Provided equipment	Installation guide
--------------------	--------------------

Physical

Color	Black
Depth	287.99 in (731.5 cm)
Height	2.52 in (6.4 cm)
Net Weight	7.61 lb(US) (3.45 kg)
Width	2.01 in (5.1 cm)

Input

Plug standard	NEMA L21-20P
Permissible voltage	200...240 V
Max line current	20 A
Nominal Input Voltage	3 phase

Output

Maximum Total Current Draw per Phase	20 A
Output voltage	120 V 208 V 3 phase

Conformance

Product certifications	UL Listed
------------------------	-----------

Ordering and shipping details

GTIN	00731304233015
Package weight(Lbs)	8.31 lb(US) (3.77 kg)

Packing Units

Package 1 Height	4.02 in (10.2 cm)
Package 1 width	12.01 in (30.5 cm)
Package 1 Length	17.52 in (44.5 cm)

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------