



Main

Range	PratiKa
Product or Component Type	Socket
Device short name	PratiKa socket
Plug, socket category	Low voltage
Poles description	2P + E
Network type	AC
Outlet standard	Industrial

Complementary

Mounting Mode	Wall-mounted
Plug, socket, control station shape	Angled
Line Rated Current	16 A
[Ue] rated operational voltage	200...250 V
Network Frequency	50/60 Hz
Ground lug clockwise position	6 h
Plug, socket material	Housing self-extinguishing engineering polymer
Contacts material	Pins stainless steel Sleeves nickel plated brass Springs stainless steel
Connections - Terminals	Captive screws, completely loosened
Cable cross section	0.00...0.01 in ² (1...4 mm ²)
Cable outer diameter	0.31...0.59 in (8...15 mm)
Cable entry	Cable gland
Thread type	Pg 16
Product Weight	0.71 lb(US) (0.324 kg)
Base dimension	80 x 100 mm
Height	6.10 in (155 mm)
Width	3.15 in (80 mm)
Depth	4.96 in (126 mm)
Color	Gray RAL 7035)
Voltage colour	Blue

Environment

Standards	EN 60309-2 EN 60309-1
IP degree of protection	IP67 conforming to IEC 60529
IK degree of protection	IK08 EN 62262
Fire resistance	1562 °F (850 °C) IEC 60695-2-11
Relative humidity	50 % 104 °F (40 °C) 70 % 86 °F (30 °C) 90 % 68 °F (20 °C)
Ambient air temperature for operation	95 °F (35 °C) 86400 s)

Ordering and shipping details

Category	01078 - DE2 MISC
Discount Schedule	DE2
GTIN	3303430831549
Nbr. of units in pkg.	1
Package weight(Lbs)	9.81 oz (278 g)
Returnability	No
Country of origin	IT

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.15 in (8 cm)
Package 1 width	4.92 in (12.5 cm)
Package 1 Length	5.91 in (15 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	4
Package 2 Weight	2.85 lb(US) (1.294 kg)
Package 2 Height	10.24 in (26 cm)
Package 2 width	6.69 in (17 cm)
Package 2 Length	10.63 in (27 cm)
Unit Type of Package 3	S03
Number of Units in Package 3	8
Package 3 Weight	6.78 lb(US) (3.075 kg)
Package 3 Height	11.81 in (30 cm)
Package 3 width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------