

SBP20KP

APC Service Bypass Panel 200/208/230/240V
125A HW Input/Output



Overview

Lead time	Usually in Stock
-----------	------------------



Main

Main Input Voltage	200 V 208 V 220 V 230 V 240 V 3 phase 3 phase 3 phase
Main Output Voltage	200 V 208 V 220 V 230 V 240 V
Output connector type	Hard Wire 3-wire (H N + E) 1 Hard Wire 3-wire (2PH + G) 1
Number of rack unit	4U
Number of cables	1
Provided Equipment	Installation guide Rack Mounting brackets User Manual

Physical

Color	Black
Height	7.01 in (17.8 cm)
Width	17.01 in (43.2 cm)
Depth	21.81 in (55.4 cm)
Net Weight	42.59 lb(US) (19.32 kg)
Mounting Location	Front
Mounting preference	Lower
Mounting Mode	Rack-mounted

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Input

Input Frequency	50/60 Hz
Number of input connectors	1 Hard Wire 3-wire (H N + E) 1 Hard Wire 3-wire (2PH + G) 1 Hard Wire 5-wire (3PH + N + G)
Acceptable Input Voltage	200...240 V
Max line current	125 A
Input current limits	125 A
Load Capacity	20000 VA
Load Power Factor Range	0...1

Output

Maximum Total Current Draw per Phase	125 A
Protection Type	Circuit breaker
Efficiency	99 %

Conformance

Product Certifications	CSA GOST
Standards	EN 60950 IEC 60950 IEC 60950 UL 1778

Environmental

Ambient Air Temperature for Operation	-4...122 °F (-20...50 °C)
Relative Humidity	0...95 %
Operating altitude	0...15000 ft
Ambient Air Temperature for Storage	-40...149 °F (-40...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	731304266952
Package weight(Lbs)	69.14 lb(US) (31.36 kg)

Packing Units

Package 1 Height	12.01 in (30.5 cm)
Package 1 width	24.02 in (61 cm)
Package 1 Length	33.27 in (84.5 cm)

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

Contractual warranty

Warranty	2 years (parts only)
----------	----------------------