

SBP2200RM

APC SERVICE BYPASS PDU, 120V 20AMP W/ (6) NEMA 5-15R AND (2) 5-20R



Overview

Lead time	Usually in Stock
-----------	------------------



Main

Main Input Voltage	120 V
Main Output Voltage	120 V
Input Connection Type	NEMA 5-20P
Number of rack unit	2U
Cable length	8 ft (2.44 m)
Number of cables	1
Provided Equipment	User Manual Rack Mounting brackets

Physical

Color	Black
Height	3.50 in (8.9 cm)
Width	17.01 in (43.2 cm)
Depth	2.99 in (7.6 cm)
Net Weight	6.50 lb(US) (2.95 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Rack-mounted

Input

Input Frequency	50/60 Hz
Acceptable Input Voltage	100...125 V
Max line current	20 A
Input current limits	20 A
Load Capacity	2200 VA
Load Power Factor Range	0...1

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Output

Maximum Total Current Draw per Phase	20 A
Number of power socket outlets	6 NEMA 5-15R 2 NEMA 5-20R
Number of power socket outlets	10
Protection Type	Circuit breaker
Cord Length	4 ft (1.22 m)
Efficiency	99 %

Conformance

Product Certifications	TÜV
------------------------	-----

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...15000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	731304266754
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.94 in (15.1 cm)
Package 1 Width	11.61 in (29.5 cm)
Package 1 Length	18.23 in (46.3 cm)
Package 1 Weight	8.38 lb(US) (3.8 kg)

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------