

SURT192RMXLBP2

APC Smart-UPS RT192V RM Battery Pack 2 Rows



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Number of rack unit	6U
Battery Type	VRLA
Provided Equipment	All required connectors Rack Mounting brackets User Manual

Physical

Color	Black
Height	10.35 in (26.3 cm)
Width	17.01 in (43.2 cm)
Depth	29.09 in (73.9 cm)
Net Weight	400.84 lb(US) (181.82 kg)
Mounting Mode	Rack-mounted

Conformance

Standards	OSHDP
-----------	-------

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...95 % non-condensing
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...95 % Non-condensing

Batteries & Runtime

Battery Slots Empty	0
Included Battery Modules	0
Device mounting	19 inch Battery tray
Battery Voltage	192V
RBC Quantity	4

Ordering and shipping details

GTIN	731304255734
Package weight(Lbs)	486.01 lb(US) (220.45 kg)

Packing Units

Package 1 Height	17.01 in (43.2 cm)
Package 1 width	24.02 in (61 cm)
Package 1 Length	39.49 in (100.3 cm)
Number of Units in Package 3	1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------