

SYBFXR3RM

APC SYMMETRA 3 Battery RACKMOUNT XR FRAME (208/120V REGIONS)



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Number of rack unit	5U
Number of cables	1
Battery Type	Lead-Acid battery
Provided Equipment	Installation guide User Manual

Physical

Color	Black
Height	8.46 in (21.5 cm)
Width	18.58 in (47.2 cm)
Depth	27.01 in (68.6 cm)
Net Weight	59.13 lb(US) (26.82 kg)
Mounting Mode	Rack-mounted

Conformance

Product Certifications	CSA
Standards	UL 1778

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...15000 ft (0.00...4572.00 m)
Storage Relative Humidity	0...95 %

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Batteries & Runtime

Battery Placement	Battery Cabinet
Battery Slots Empty	3
Included Battery Modules	0
Battery manufacturer	Panasonic
Device mounting	Enclosed battery cabinet
RBC Quantity	3

Ordering and shipping details

GTIN	731304233787
Package weight(Lbs)	68.17 lb(US) (30.92 kg)

Packing Units

Package 1 Height	13.50 in (34.3 cm)
Package 1 width	23.58 in (59.9 cm)
Package 1 Length	38.58 in (98 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Lead free	Yes
Mercury free	Yes
RoHS exemption information	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------