



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Number of cables	1
Battery Type	VRLA
Provided Equipment	Installation guide User Manual

Physical

Color	Black
Height	82.01 in (208.3 cm)
Width	24.02 in (61 cm)
Depth	34.02 in (86.4 cm)
Net Weight	551.16 lb(US) (250 kg)
Mounting Mode	Not rack-mountable

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Operating altitude	0...3333 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %

Batteries & Runtime

Battery Placement	Battery Cabinet
Battery blocks per string	4
Battery Slots Empty	0
Included Battery Modules	0
Device mounting	19 inch Battery tray

Ordering and shipping details

GTIN	731304207351
Package weight(Lbs)	601.27 lb(US) (272.73 kg)

Packing Units

Package 1 Height	82.01 in (208.3 cm)
Package 1 width	30.00 in (76.2 cm)
Package 1 Length	40.00 in (101.6 cm)
Number of Units in Package 3	2

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Lead free	Yes
Take-back	Take-back program available

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------