

Product data sheet

Characteristics

TCSESPU093F2CU0

switch, Modicon Networking, premium unmanaged switch, 7 ports for copper, 2 ports for fiber optic multimode



Main

Range of product	Modicon Networking
Product or component type	Ethernet TCP/IP unmanaged switch
Communication port protocol	Ethernet TCP/IP
Port Ethernet	10/100BASE-TX - 7 port(s) copper cable 100BASE-FX - 2 port(s) fiber optic
Maximum number of switches in cascade	Unlimited

Complementary

Integrated connection type	Shielded RJ45 copper cable Duplex SC fiber optic
Transmission support medium	Twisted shielded pairs cable CAT 5E for copper cable Multimode optical fiber for fiber optic
Maximum cable distance between devices	100 M copper cable
Optic fiber length	4 Km 62.5/125 µm 5 Km 50/125 µm
Attenuation	0...11 DB (62.2/125 µm) 0...8 DB (50/125 µm)
Ethernet service	Multicast filtering Data stream control
Communication service	Quality of Service (QoS)
[Us] rated supply voltage	12...24 V
Supply voltage limits	9.6...32 V DC SELV
Power consumption in W	6.9 W
Electrical connection	Removable connector 6 ways power supply
Mounting support	35 mm symmetrical DIN rail
Marking	CE UL RCM
Local signalling	1 dual colour LED (green/yellow) for P1 P2 power supplies 1 LED per channel (yellow) for data rate (ETH LINK) 1 dual colour LED (green/yellow) for link status
Ethernet cabling system	TF switches
Width	56 Mm
Height	135 Mm
Depth	117 Mm
Net weight	0.510 Kg

Environment

Ambient air temperature for operation	-40...70 °C
Relative humidity	10...95 % non-condensing
IP degree of protection	IP40
Directives	2014/35/EU - low voltage directive 2014/30/EU - electromagnetic compatibility
Standards	UL 61010 EN/IEC 61131 UL 121201
Product certifications	CE[RETURN]UL[RETURN]RCM[RETURN]EAC[RETURN]UKCA[RETURN]D-NV[RETURN]CSA C22-2 No 213

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.0 Cm
Package 1 Width	16.0 Cm
Package 1 Length	23.5 Cm
Package 1 Weight	800.0 G
Unit Type of Package 2	S04
Number of Units in Package 2	8
Package 2 Height	30.0 Cm
Package 2 Width	40.0 Cm
Package 2 Length	60.0 Cm
Package 2 Weight	6.4 Kg

Offer Sustainability

Sustainable packaging	No
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Take-back	No

Contractual warranty

Warranty (in months)	18
----------------------	----

Product Life Status : **End of commerc. announced**