

# Product data sheet

## Characteristics

### TSXCANCADD03

CANopen cordset - molded female SUB-D9  
connectors - standard - IP20 - 0.3 m



#### Main

Range of Product	CANopen
Bus type	CANopen
Accessory / separate part category	Connection accessories
Accessory / Separate Part Type	Connecting cable
Accessory / separate part destination	CANopen bus
Cable length	0.98 ft (0.3 m)

#### Complementary

Electrical connection	2 female connectors SUB-D 9
Marking	CE
Net Weight	0.20 lb(US) (0.091 kg)

#### Environment

IP Degree of Protection	IP20
-------------------------	------

#### Ordering and shipping details

Category	22531-PLCS, TWIDO, TWD
Discount Schedule	PC12
GTIN	3595863860153
Returnability	No
Country of origin	PT

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.39 in (1.0 cm)
Package 1 Width	5.91 in (15.0 cm)
Package 1 Length	7.87 in (20.0 cm)
Package 1 Weight	3.21 oz (91.0 g)
Unit Type of Package 2	S03
Number of Units in Package 2	70
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	14.97 lb(US) (6.79 kg)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#"> EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#"> China RoHS Declaration</a>
RoHS exemption information	<a href="#"> Yes</a>

## Contractual warranty

Warranty	18 months
----------	-----------