



Main

Range	TeSys
Device short name	GAC0
Product or Component Type	Auxiliary contact block
Product Compatibility	TeSys GC TeSys GY
Mounting Location	Right side
Pole contact composition	1 C/O
[Ue] rated operational voltage	250 V
[Ith] conventional free air thermal current	5 A 122 °F (50 °C)

Complementary

[Ui] rated insulation voltage	500 V IEC 60947-5 500 V VDE 0110
Mechanical durability	1 Mcycles
Connections - terminals	Screw clamp terminals 0.00 in ² (2.5 mm ²)solid Screw clamp terminals 0.00 in ² (2.5 mm ²)flexible
Tightening torque	7.08 lbf.in (0.8 N.m) screw clamp terminals
Height	3.19 in (81 mm)
Width	0.34 in (8.75 mm)
Depth	2.36 in (60 mm)
Product Weight	0.04 lb(US) (0.016 kg)

Environment

Standards	IEC 60947-5
Product Certifications	OVE CEBEC VDE NF-USE
IP degree of protection	IP20 conforming to VDE 0106
Protective treatment	TC
Ambient Air Temperature for Operation	23...122 °F (-5...50 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Operating altitude	<= 9842.52 ft (3000 m) without derating

Ordering and shipping details

Category	18402 - WORLD SERVICE PARTS(CONTROL ACCESS)
Discount Schedule	CP10
GTIN	3389110707618
Nbr. of units in pkg.	1
Package weight(Lbs)	1.51 oz (42.9 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.83 in (2.1 cm)
Package 1 width	2.95 in (7.5 cm)
Package 1 Length	3.39 in (8.6 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	17.21 oz (488 g)
Package 2 Height	3.23 in (8.2 cm)
Package 2 width	3.82 in (9.7 cm)
Package 2 Length	9.06 in (23 cm)
Unit Type of Package 3	S03
Number of Units in Package 3	80
Package 3 Weight	9.55 lb(US) (4.331 kg)
Package 3 Height	11.81 in (30 cm)
Package 3 width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------