



Main

Range of Product	Vijeo Designer
Product or Component Type	Configuration software
Language	German Italian English Spanish Chinese French Portuguese
Format	DVD-ROM
Previous software version	V6.1
Type of license	Single (1 station)
Software Version	V6.2

Complementary

Range compatibility	Harmony XBT GT Harmony STO & STU Harmony XBT GH Harmony HMI GTO Harmony iPC Harmony XBT GK Harmony XBT GTW Harmony Smart Harmony Compact iPC
Software Designation	Vijeo Designer
System requirements	Processor suitable for operating system Windows 7 Professional 32/64 bit Processor suitable for operating system Windows 8.1 Processor suitable for operating system Windows 10 Professional 32/64 bit
Communication Port Protocol	UniTE TCP/IP Ethernet/IP Explicit Toyopuc PC3J USB Sysmacway Modbus TCP master Simatic Profibus DP ELAU PacDrive Modbus 32-bit extensions Uni-Telway Modbus Plus Fipio/Fipway ROC Plus MELSEC Modbus RTU master Allen-Bradley
Provided Equipment	Vijeo Designer software Acrobat Reader
Software Function	34 western alphabets 9999 alarms 8000 variables 4 asian alphabets Sharing up to 300 variables 2 middle eastern alphabets
Audio video coding standard	JPEG

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	22569-MAGELIS XBT-GT (AND XBT-G)
Discount Schedule	MC2
GTIN	3606480712890
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.79 in (2.000 cm)
Package 1 Width	5.28 in (13.400 cm)
Package 1 Length	6.22 in (15.800 cm)
Package 1 Weight	3.88 oz (110.000 g)
Unit Type of Package 2	S02
Number of Units in Package 2	16
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	4.60 lb(US) (2.086 kg)

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes