

Product data sheet

Specifications

SQUARE D



Disconnect switch, 9422T, fixed flange rod depth, max 30A rated, 20hp at 575VAC, fuse type J/K/H/R

9422FTCF33

Product availability: Stock - Normally stocked in distribution facility

Main

Range	9422T
Product	Disconnect Switch
Disconnect Type	Fusible disconnect switch

Complementary

Mounting Type	Flange rod fixed depth
Current Rating	30 A
Horsepower Rating	7.5 hp 200 V AC 7.5 hp 230 V AC 15 hp 460 V AC 20 hp 575 V AC 5 hp 250 V DC
Fuse Rating	60 A 250 V 30 A 600 V
Handle Type	Ordered separately
Fuse Type	J K H R

Environment

Certifications	UL Recognized CSA
----------------	----------------------

Ordering and shipping details

Category	US1CP1018079
Discount Schedule	CP10
GTIN	785901162186
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	7.50 in (19.05 cm)
Package 1 Width	11.00 in (27.94 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Length	16.50 in (41.91 cm)
Package weight(Lbs)	3.111 lb(US) (1.411 kg)

Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
California proposition 65	<p>WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov</p>
PVC free	Yes

Use Again

Repack and remanufacture

Take-back	No
-----------	----