

# Product data sheet

Specifications



Handles and front plates, TeSys Control, black handle, black front, 1-3 padlocking, 4 screws fixing, for VN12/VN20/V02-V2

KAF1PZ

## Main

|                           |                          |
|---------------------------|--------------------------|
| Range                     | TeSys                    |
| Device short name         | KAF1                     |
| Product or component type | Rotary handle            |
| Product compatibility     | VN20<br>VN12<br>V02...V2 |
| Handle colour             | Black                    |

## Complementary

|                              |                          |
|------------------------------|--------------------------|
| Handle front plate colour    | Black                    |
| Rotary handle padlocking     | 1 to 3 padlocks 4...8 mm |
| Marking                      | 0 - 1                    |
| Fixing mode                  | By 4 screws              |
| Handle front plate dimension | 60 x 60 mm               |
| Height                       | 60 mm                    |
| Width                        | 60 mm                    |
| Product weight               | 0.075 kg                 |

## Environment

|                         |      |
|-------------------------|------|
| IP degree of protection | IP65 |
|-------------------------|------|

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 7.800 cm  |
| Package 1 Width              | 6.500 cm  |
| Package 1 Length             | 6.500 cm  |
| Package 1 Weight             | 69.000 g  |
| Unit Type of Package 2       | S03       |
| Number of Units in Package 2 | 45        |
| Package 2 Height             | 30.000 cm |
| Package 2 Width              | 30.000 cm |
| Package 2 Length             | 40.000 cm |

|                              |           |
|------------------------------|-----------|
| Package 2 Weight             | 3.671 kg  |
| Unit Type of Package 3       | P06       |
| Number of Units in Package 3 | 360       |
| Package 3 Height             | 75.000 cm |
| Package 3 Width              | 60.000 cm |
| Package 3 Length             | 80.000 cm |
| Package 3 Weight             | 38.220 kg |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

## Environmental footprint

Total lifecycle Carbon footprint **30**

Environmental Disclosure [Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard **Yes**

Packaging without single use plastic **No**

[EU RoHS Directive](#) **Compliant**

California proposition 65 **WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to [www.P65Warnings.ca.gov](#)**

## Use Again

### Repack and remanufacture

End of life manual availability **No need of specific recycling operations**

Take-back **No**

WEEE Label **The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins**