

8501XUDO40V67

NEMA Control Relay, Type X, utility, 10A resistive at 600 VAC, 4 normally open contacts, 250 VDC coil



Main

Range	8501X
Relay Type	Utility
Product	Relay
Current Rating	10 A AC 5 A DC
Contact Configuration	4 NO 4 standard contact cartridges
Number of Poles	4P
Coil Voltage	250 V DC
Voltage Rating	250 V DC
Mounting Type	Panel
Operating Temperature	-40...160 °F (-40...71 °C)
Electrical Connection	Screw clamp terminals
Certifications	UL Listed CE CSA
Operating Time	37 ms - pick-up 21 ms - drop-out
Height	3.56 in (90.42 mm)
Width	2.23 in (56.64 mm)
Depth	5.17 in (131.32 mm)

Ordering and shipping details

Category	21157-8501 XDO (DC)
Discount Schedule	CP2
GTIN	785901457978
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	32.00 oz (907.185 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes

China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------