



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	AC 1 phase
Number of rack unit	42U
Provided Equipment	Installation guide Operations and maintenance manual

General

Air Discharge Patterns	Horizontal
Intake Air	Rear Return
Air flow	2912 ft ³ /min (1374.31 l/s)

Physical

Color	Dark grey
Height	78.39 in (1991 mm)
Width	11.81 in (300 mm)
Depth	43.11 in (1095 mm)
Net Weight	411.16 lb(US) (186.5 kg)

Input

Input power	930 W
Input Frequency	50-60 Hz

Conformance

Product Certifications	CE UL RCM
------------------------	-----------------

Communications & Management

Control panel	Touch Screen LCD User Interface
Audible Alarm	Audible and visible alarms prioritized by severity

Ordering and shipping details

GTIN	731304422938
------	--------------

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	1 year (parts only), 1 year on-site repair or replace with factory authorized Start-Up
----------	--