

Product data sheet

Characteristics

8903LO30V01

8903L electrically held lighting contactor, 3 P, 3 NO, 30 A, 600 V, 24 V 60 Hz c

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Product or component type	Electrically Held Lighting Contactor
Range of product	8903L
Control Circuit	Separate control circuit

Complementary

Control Circuit Voltage	24 V AC 60 Hz
Inrush power in VA	150 VA 60 Hz
Hold-in power consumption in VA	30 VA 60 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number of Poles	3P 3 NO
Control Unit	No control units
Pilot Light	No indicator
Electrical connection	Screw-clamp terminals
Height	5 in (127 mm)
Depth	3.11 in (79 mm)
Width	2.87 in (73 mm)

Environment

Enclosure Type	Not rated (open device)
Product certifications	CSA UL listed

Ordering and shipping details

Category	21321 - 8903 L (NOT LX)
Discount Schedule	CP1
GTIN	00785901022961
Nbr. of units in pkg.	1
Package weight(Lbs)	2.54
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1431 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------