



Main

Range	TeSys
Device short name	Green pilot light
Product or Component Type	Pilot light

Complementary

Local signalling	Green light
[Ue] rated operational voltage	230...240 V
Range compatibility	TeSys (TeSys GV2) circuit breaker
Accessory / separate part category	Lighting accessories
Diameter	0.67 in (17 mm)

Ordering and shipping details

Category	22367-MANUAL STR PROTECTOR - GV2
Discount Schedule	I11
GTIN	3389110487152
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.36 in (6.0 cm)
Package 1 Width	3.23 in (8.2 cm)
Package 1 Length	3.94 in (10.0 cm)
Package 1 Weight	0.35 oz (10.0 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	2.36 in (6.0 cm)
Package 2 Width	3.23 in (8.2 cm)
Package 2 Length	3.94 in (10.0 cm)
Package 2 Weight	3.77 oz (107.0 g)
Unit Type of Package 3	S01
Number of Units in Package 3	80
Package 3 Height	5.91 in (15.0 cm)
Package 3 Width	5.91 in (15.0 cm)
Package 3 Length	15.75 in (40.0 cm)
Package 3 Weight	2.33 lb(US) (1.059 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------