

Product data sheet

Characteristics

LA1LC070F

TeSys Integral - undervoltage trip - 110 V AC 50 Hz - 0.2 s

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range	TeSys
Device short name	LA1LC
Product or component type	Undervoltage trip
Product compatibility	LD4 LD5
Range compatibility	TeSys Integral contactor breaker

Complementary

[Uc] control circuit voltage	110 V AC 50 Hz 110...120 V AC 60 Hz
Time delay	0.2 s
Voltage release type	Undervoltage release
Control circuit voltage limits	0.8...1.1 Uc
Threshold tripping voltage	0.35...0.7 Uc
Inrush power in VA	8 VA AC
Hold-in power consumption in VA	4 VA AC
Quantity per set	Set of 10
Product weight	0.33 lb(US) (0.15 kg)

Ordering and shipping details

Category	22384 - STARTERS,INTEGRAL,ACCESS
Discount Schedule	I11
GTIN	00785901223696
Nbr. of units in pkg.	1
Package weight(Lbs)	0.37
Returnability	N
Country of origin	CZ

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Styrene, which is known to the State of California to cause cancer.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------