



Overview

Presentation	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
Lead time	Usually Ships within 3 Weeks

Main

Main Input Voltage	3 phase
Main Output Voltage	230 V 400 V 3 phase
Provided Equipment	Installation guide

Physical

Color	Gray
Height	5.98 in (15.2 cm)
Width	10.51 in (26.7 cm)
Depth	12.01 in (30.5 cm)
Net Weight	68.14 lb(US) (30.91 kg)

Input

Input Frequency	50 Hz
Max line current	63 A

Output

Maximum Total Current Draw per Phase	63 A
Number of power socket outlets	1 IEC 309

Conformance

Product Certifications	CE VDE
------------------------	-----------

Environmental

Ambient Air Temperature for Operation	32...86 °F (0...30 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...104 °F (-15...40 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...15000 ft (0.00...4572.00 m)

Ordering and shipping details

GTIN	731304283669
Package weight(Lbs)	72.16 lb(US) (32.73 kg)

Packing Units

Package 1 Height	9.02 in (22.9 cm)
Package 1 width	20.00 in (50.8 cm)
Package 1 Length	20.00 in (50.8 cm)

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------