

# Product data sheet

Specifications

SQUARE D



NEMA motor starter, Type S, nonreversing, Size 5, 270A, 200HP at 460VAC, up to 100kA SCCR, 3 phase, 3 pole, Motor Logic, 480VAC coil, open [TAA]

8536SGO1V06H30

Product availability: Stock - Normally stocked in distribution facility

## Main

|               |               |
|---------------|---------------|
| Product Type  | Motor starter |
| Product Range | S             |
| Starter Type  | Non reversing |

## Complementary

|                        |                                                                                                                                                                                                                                       |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| NEMA Size              | 5                                                                                                                                                                                                                                     |
| Rated Current          | 270 A                                                                                                                                                                                                                                 |
| Number of Poles        | 3P                                                                                                                                                                                                                                    |
| Maximum Voltage Rating | 600 V AC                                                                                                                                                                                                                              |
| Phase                  | 3 phase                                                                                                                                                                                                                               |
| Type of Overload       | Solid state Motor Logic class 10/20                                                                                                                                                                                                   |
| Horsepower Rating      | 75 HP 200 V AC<br>100 HP 230 V AC<br>200 HP 460 V AC<br>200 HP 575 V AC                                                                                                                                                               |
| SCCR                   | Circuit-breaker 400 A maximum: 100 kA at 480 V AC<br>Fuse J 400 A maximum: 100 kA at 600 V AC<br>Fuse T 400 A maximum: 100 kA at 600 V AC<br>Fuse RK1 400 A maximum: 100 kA at 600 V AC<br>Fuse RK5 400 A maximum: 100 kA at 600 V AC |
| Coil Voltage           | 440 V AC 50 Hz<br>480 V AC 60 Hz                                                                                                                                                                                                      |
| Control Circuit Type   | Common control circuit                                                                                                                                                                                                                |
| Control Units          | No control units                                                                                                                                                                                                                      |
| Pilot Light            | Without pilot light                                                                                                                                                                                                                   |
| Auxiliary Contacts     | Uden                                                                                                                                                                                                                                  |
| Terminal Type          | Screw clamp terminals                                                                                                                                                                                                                 |
| Height                 | 17.56 in (446.02 mm)                                                                                                                                                                                                                  |
| Width                  | 8.56 in (217.42 mm)                                                                                                                                                                                                                   |
| Depth                  | 8.75 in (222.25 mm)                                                                                                                                                                                                                   |

## Environment

|                |                         |
|----------------|-------------------------|
| Enclosure Type | Not rated (open device) |
|----------------|-------------------------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                |                          |
|----------------|--------------------------|
| Certifications | UL Listed<br>CSA<br>NEMA |
|----------------|--------------------------|

## Ordering and shipping details

|                   |              |
|-------------------|--------------|
| Category          | US10CP121194 |
| Discount Schedule | 0CP1         |
| GTIN              | 785901874850 |
| Returnability     | Yes          |
| Country of origin | MX           |

## Packing Units

|                        |                           |
|------------------------|---------------------------|
| Unit Type of Package 1 | PCE                       |
| Nbr. of units in pkg.  | 1                         |
| Package 1 Height       | 50.79 in (129.0 cm)       |
| Package 1 Width        | 25.39 in (64.5 cm)        |
| Package 1 Length       | 49.53 in (125.8 cm)       |
| Package weight(Lbs)    | 59.468 lb(US) (26.974 kg) |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

|  Materials and Substances |                                                                                                                                                                                                                                                                                             |
|------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Packaging made with recycled cardboard                                                                     | No                                                                                                                                                                                                                                                                                          |
| Packaging without single use plastic                                                                       | No                                                                                                                                                                                                                                                                                          |
| EU RoHS Directive                                                                                          | Not compliant                                                                                                                                                                                                                                                                               |
| California proposition 65                                                                                  | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |

Use Again

|  Repack and remanufacture |    |
|------------------------------------------------------------------------------------------------------------|----|
| Take-back                                                                                                  | No |