

Product data sheet

Specifications

SQUARE D



Mini circuit breaker, E-Frame, 20A, 1 pole, 277VAC, 100kA max, bolt on [TAA]

EJB14020

Product availability: Stock - Normally stocked in distribution facility

Main

Range	125 A Frame EDB-EGB-EJB
Product Type	Miniature circuit-breaker
Device Short Name	EJB
Module Type	E-Frame
Trip Unit Rating	875 A

Complementary

Rated Current	20 A
Maximum Operating Voltage	277 V AC
AWG Gauge	AWG 12...AWG 6 aluminium AWG 14...AWG 6 copper
Breaking Capacity	65 kA 240 V AC 65 kA 277 V AC 100 kA 120 V AC 65 kA 120/240 V AC
Circuit Breaker Application	Switching Duty rated HID rated HACR rated
Electrical Connection	Lugs aluminium
Holding Current	270 A
Local Signalling	Trip indicator
Mounting Mode	Bolt-on
Number of Poles	1
Number of Spaces	1
Number of Spaces Required	1
Product Destination	NF panelboard
Protect Type	Overload Short-circuit
Trip Unit Technology	Thermal-magnetic
Breaking Capacity Code	J
Tightening Torque	30.09 lbf.in (3.4 N.m) 0.004...0.02 in ² (2.5...16 mm ²) (AWG 14...AWG 6)
Height	5.66 in (143.76 mm)
Width	0.98 in (24.89 mm)
Depth	4.05 in (102.87 mm)
Product Weight	2 lb(US) (0.9 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Product Certifications	cULus
Ambient Air Temperature for Operation	104 °F (40 °C)

Ordering and shipping details

Category	US10DE200937
Discount Schedule	ODE2
GTIN	785901130505
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	1.80 in (4.572 cm)
Package 1 Width	6.20 in (15.748 cm)
Package 1 Length	10.30 in (26.162 cm)
Package weight(Lbs)	21.920 oz (621.421 g)
Unit Type of Package 2	PAL
Number of Units in Package 2	1008
Package 2 Height	40.00 in (101.600 cm)
Package 2 Width	40.00 in (101.600 cm)
Package 2 Length	48.00 in (121.920 cm)
Package 2 Weight	1381.0010 lb(US) (626.411 kg)

Compliance

Compliance	TAA
------------	-----

Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle) **54**

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard **Yes**

Packaging without single use plastic **No**

EU RoHS Directive **Not applicable, out of EU RoHS legal scope**

SCIP Number **8781af64-acd9-485c-9a86-abcd458e3**

REACH Regulation [REACH Declaration](#)

Use Again


Repack and remanufacture

Circularity Profile [End of Life Information](#)

Take-back **No**

Technical Illustration

Dimensions



All dimensions are approximate.
Also see technical drawings and/or documentation.