

# Product data sheet

Specifications



## APC NetShelter Basic Rack PDU, 0U, 30A, 200/208V, 20 C13 and 4 C19 outlet

AP7541

### Overview

<b>Presentation</b>	APC Basic Rack PDUs distribute reliable rack power distribution via a single input with multiple output receptacles. Easily mount this vertical PDU in racks or enclosures. It occupies zero U of valuable rack space, which allows space for more equipment in the rack. This vertical PDU does not require additional tools to mount into APC NetShelter Enclosures. Enables a quick recovery from overload events. Packaging Includes PDU, Installation guide, Rack Mounting brackets, Toolless Mounting Kit.
---------------------	--

<b>Lead time</b>	Usually in Stock
------------------	------------------

### Main

<b>Colour</b>	Black
<b>Product or component type</b>	PDU
<b>PDU type</b>	Basic
<b>Cord length</b>	3.05 m
<b>Number of cables</b>	1
<b>Provided equipment</b>	Installation guide Rack mounting brackets Toolless mounting kit

### Complementary

<b>Input Voltage</b>	200 V 208 V 230 V
<b>Height</b>	161.9 cm
<b>Width</b>	5.6 cm
<b>Output Voltage</b>	200 V 208 V
<b>Depth</b>	4.4 cm
<b>Product weight</b>	5.57 kg
<b>Mounting location</b>	Side
<b>Mounting preference</b>	No preference
<b>Input Plug Type</b>	NEMA L6-30P
<b>Mounting mode</b>	Rack-mounted
<b>Rack units</b>	0U
<b>USB compatible</b>	No
<b>Mounting position</b>	Vertical
<b>[In] rated current</b>	24 A

<b>Input current limits</b>	30 A
<b>Load capacity</b>	4992 VA
<b>Network frequency</b>	50/60 Hz
<b>Outlet type and quantity</b>	20 IEC 60320 C13 4 IEC 60320 C19

## Environment

<b>Product certifications</b>	cUL listed METI Denan PSE UL listed
<b>Standards</b>	CSA C22.2 No. 60950-1-03 UL 60950-1
<b>Ambient air temperature for operation</b>	0...45 °C
<b>Relative humidity</b>	0...95 %
<b>Operating altitude</b>	0...10000 ft
<b>Ambient air temperature for storage</b>	-25...65 °C
<b>Storage Relative Humidity</b>	0...95 %
<b>Storage altitude</b>	0...15240 m

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	212.1 cm
<b>Package 1 Width</b>	12.7 cm
<b>Package 1 Length</b>	15.2 cm
<b>Package 1 Weight</b>	6.48 kg

## Contractual warranty

<b>Warranty</b>	2 years repair or replace
-----------------	---------------------------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Total lifecycle Carbon footprint	137
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Use Better

### Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
<a href="#">EU RoHS Directive</a>	Compliant
REACH Regulation	<a href="#">REACH Declaration</a>
Halogen-free status	Product contains halogen above thresholds

### Energy efficiency

Energy Efficiency Optimized	<b>Energy efficient product</b>
-----------------------------	---------------------------------

## Use Again

### Repack and remanufacture

End of life manual availability	<a href="#">End of Life Information</a>
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative

---

