

Product data sheet

Specifications



APC NetShelter SV, Server Rack Enclosure, 42U, 600W x 1060 D mm, with Sides, Black, Single Rack Unassembled

AR2400FP1

Overview

Presentation	Not all installation sites have space clearance required to move and install standard height enclosures. This unassembled Universal IT enclosure option for low to medium density server and networking applications is packaged for transport through narrow spaces and assembly at the installation site.
---------------------	---

Lead time	Usually in Stock
------------------	------------------

Main

Product or component type	Rack enclosure
Number of rack unit	42U
Provided equipment	Adjustable vertical mounting rails Baying hardware Casters Door handle Doors Installation guide Key(s) Keyed-alike doors and side panels Leveling feet Mounting hardware Pre-installed casters 2 x plate 4 x bolt down brackets Roof Side panels Side panel lock Slam latches

Physical

Height	205.7 cm
Width	60 cm
Depth	106 cm
Product weight	112.2 kg
Colour	Black
Mounting preference	No preference
Mounting mode	Not rack-mountable
Maximum mounting depth	77.72 cm
Minimum mounting depth	16.76 cm
Rack width	19"

Marking	14 gauge EIA mounting rail 16 gauge front door 18 gauge post 16 gauge rear door 19 gauge roof 18 gauge side panels
Permanent permissible load	459.9 kg dynamic 1000.2 kg static

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
------------------	-----------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	81 cm
Package 1 Width	68.3 cm
Package 1 Length	223 cm
Package 1 Weight	220.656 kg

Contractual warranty

Warranty	5 year repair or replace
-----------------	--------------------------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Total lifecycle Carbon footprint	670
----------------------------------	-----

Use Better

Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACH Regulation	REACH Declaration

Use Again

Repack and remanufacture

End of life manual availability	End of Life Information
Take-back	No

Image of product / Alternate images

Alternative















