

Product data sheet

Characteristics

8911DP SG32V09

Starter, Definite Purpose, nonreversing, 30A,
2 pole, 1 phase, 208 to 240 VAC coil, melting
alloy overload, NEMA 1



Main

Product	Definite Purpose Starter
Ampere Rating	30 A
Horsepower Rating	2 Hp 115 V AC, 1 phase 5 hp 230 V AC, 1 phase
Maximum Voltage Rating	600 V AC
Control Circuit Voltage	220 V AC 50 Hz 208...240 V AC 60 Hz
Phase	1 phase

Complementary

Enclosure Material	Painted sheet steel
Enclosure Rating	NEMA 1
Locked Rotor Amperes	180 A 230 V AC 150 A 460 V AC 120 A 575 V AC
Number of Poles	2P
Range	DPS
Overload Type	Melting alloy
Number of Thermal Units	1

Ordering and shipping details

Category	21381-8911 DP
Discount Schedule	CP1
GTIN	785901024699
Nbr. of units in pkg.	1
Package weight(Lbs)	5.75 lb(US) (2.608 kg)
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	6.60 in (16.764 cm)
Package 1 width	7.10 in (18.034 cm)
Package 1 Length	11.20 in (28.448 cm)

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------