



### Main

Range of Product	Harmony 9001K
Product or Component Type	Security control station
Device short name	9001KY
Lock type	Complete with core, 7 tumbler pins

### Complementary

Size	30 mm
Enclosure/cubicle description	Surface mounting
Enclosure Material	Cast Aluminium
Type of Installation	Indoor/outdoor
Control station composition	1 key selector switch, spring return OPEN-CLOSE
Type of keylock	Best
Key withdrawal position	Center
Connections - terminals	Screw clamp terminal
[Ue] rated operational voltage	300 V
[Ie] rated operational current AC	15 A
Net Weight	3.55 lb(US) (1.61 kg)

### Environment

NEMA degree of protection	NEMA 3R
Environmental characteristic	Waterproof
Product Certifications	CE UL Listed CSA
Ambient Air Temperature for Operation	-13...140 °F (-25...60 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)

### Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	785901347460
Returnability	No
Country of origin	MX

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.43 in (29.032 cm)
Package 1 Width	4.50 in (11.43 cm)
Package 1 Length	29.03 in (73.742 cm)
Package 1 Weight	3.75 lb(US) (1.701 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------