

# Product data sheet

## Characteristics

# ACRC301S

InRow RC, 300mm, Chilled Water, 100-240V, 50/60 Hz - ST



### Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

### Main

Main Input Voltage	100...120 V 200...240 V
Plug standard	IEC 60309 16 A 2P+E NEMA L5-20P
Number of rack unit	42U
Number of cables	2
Provided Equipment	Installation guide Operations and maintenance manual

### General

Air Discharge Patterns	Horizontal
Intake Air	Rear Return
Air flow	3200 ft <sup>3</sup> /min (1510.23 l/s)
Minimum Water Inlet Temperature	45 °F (7 °C)
Condensate Pump Capacity	1.3 Gal/hr(US) (0.00 m3/h)

### Physical

Color	Black
Height	78.39 in (199.1 cm)
Width	11.81 in (30 cm)
Depth	43.11 in (109.5 cm)
Net Weight	405.65 lb(US) (184 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

### Input

Number of Power Feeds	2
Input power	800 W
Input Frequency	50/60 Hz

## Conformance

Product Certifications	C-tick CE GOST MEA VDE
Standards	EN 55022 Class A EN 55024 EN 60950 IEC 60950 IEC 61000-3-2 IEC 61000-3-3

## Communications & Management

Control panel	Multi-function LCD status and control console
Audible Alarm	Audible and visible alarms prioritized by severity

## Ordering and shipping details

GTIN	731304301387
Package weight(Lbs)	423.29 lb(US) (192 kg)

## Packing Units

Package 1 Height	83.39 in (211.8 cm)
Package 1 width	29.37 in (74.6 cm)
Package 1 Length	44.76 in (113.7 cm)
Number of Units in Package 3	1

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>

## Contractual warranty

Warranty	1 year (parts only)
----------	---------------------