

Product data sheet

Characteristics

APCRBC105

APC Replacement Battery Cartridge #105 with 2 Year Warranty



Overview

Lead time	Usually in Stock
-----------	------------------



Main

Number of cables	1
Battery Type	Lead-Acid battery
Provided Equipment	All required connectors Battery recycling guide Metallic battery tray or enclosure Reusable packaging Installation guide

Physical

Height	4.25 in (10.8 cm)
Width	6.50 in (16.5 cm)
Depth	22.52 in (57.2 cm)
Net Weight	54.12 lb(US) (24.55 kg)
Mounting Mode	Not rack-mountable

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	23...113 °F (-5...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...95 %

Batteries & Runtime

Battery Slots Empty	0
Included Battery Modules	0
Device mounting	Enclosed battery cartridge
Battery Voltage	48V
Additional information	The SUA48RMXLBP3U requires two(2) APCRBC105..
RBC Quantity	1

Ordering and shipping details

GTIN	731304248729
Package weight(Lbs)	58.11 lb(US) (26.36 kg)

Packing Units

Package 1 Height	10.98 in (27.9 cm)
Package 1 width	12.24 in (31.1 cm)
Package 1 Length	29.02 in (73.7 cm)
Number of Units in Package 3	16

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------