

Product data sheet

Characteristics

AR2487

NetShelter SV 48U 800mm Wide x 1060mm Deep Enclosure with Sides Black



Overview

Presentation	Wide and Tall Universal IT enclosure with increased enclosure width for more cable management options in denser server and networking applications and 48U spaces for environments that can take advantage of higher spaces and provide more mounting u-spaces at each enclosure footprint. Includes integrated vertical 1U mounting spaces adjacent the enclosures standard EIA-310 equipment mounting u-spaces that can be removed and replaced with 1U accessories.
Lead time	Usually in Stock

Main

Number of rack unit	48U
Provided equipment	Baying hardware Doors Key(S) Keyed-alike doors and side panels Leveling feet Mounting Hardware Pre-installed casters 4 x Bolt down brackets Roof Side Panels Unpacking sheet

Physical

Color	Black
Height	91.50 in (232.4 cm)
Width	31.50 in (80 cm)
Depth	41.73 in (106 cm)
Net Weight	317.02 lb(US) (143.8 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	30.60 in (77.72 cm)
Minimum Mounting Depth	6.60 in (16.76 cm)
Rack Width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 18 gauge post 16 gauge rear door 19 gauge roof 18 gauge side panels
Permanent permissible load	1014 Lb(US) (459.94 kg) dynamic 2205 lb(US) (1000.17 kg) static

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

GTIN	731304302087
Package weight(Lbs)	364.20 lb(US) (165.2 kg)

Packing Units

Package 1 Height	96.38 in (244.8 cm)
Package 1 width	35.43 in (90 cm)
Package 1 Length	45.67 in (116 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------