

# Product data sheet

## Characteristics

### AR3006SP

APC NetShelter SX, Server Rack Enclosure,  
18U, Shock Packaging, Black, 925H x 600W x  
900D mm



#### Overview

Presentation	An industry-standard server rack with height designed to easily fit through standard doorways. Ready for medium to high-density environments.
Lead time	Usually in Stock

#### Main

Number of rack unit	18U
Provided equipment	Casters Doors Key(S) Leveling feet Reusable packaging Roof Side Panels Pallet ramps

#### Physical

Color	Black
Height	36.42 in (92.5 cm)
Width	23.62 in (60 cm)
Depth	35.43 in (90 cm)
Net Weight	148.00 lb(US) (67.13 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	29.75 in (75.57 cm)
Minimum Mounting Depth	7.52 in (19.1 cm)
Rack Width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels
Permanent permissible load	900 Lb(US) (408.23 kg) dynamic 900 lb(US) (408.23 kg) static

#### Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

## Ordering and shipping details

GTIN	731304347668
Package weight(Lbs)	264.55 lb(US) (120 kg)

## Packing Units

Package 1 Height	48.03 in (122 cm)
Package 1 width	29.53 in (75 cm)
Package 1 Length	42.13 in (107 cm)
Number of Units in Package 3	1

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------