



Overview

Presentation	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
Lead time	Usually Ships within 3 Weeks

Main

Main Input Voltage	208 V
Main Output Voltage	208 V
Provided Equipment	Installation guide

Physical

Color	Black
Height	5.00 in (12.7 cm)
Width	17.48 in (44.4 cm)
Depth	15.98 in (40.6 cm)
Net Weight	9.46 lb(US) (4.29 kg)

Input

Input Frequency	60 Hz
Max line current	30 A

Output

Maximum Total Current Draw per Phase	30 A
Number of power socket outlets	1 NEMA L6-30R

Conformance

Product Certifications	UL Listed
------------------------	-----------

Environmental

Ambient Air Temperature for Operation	32...86 °F (0...30 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...104 °F (-15...40 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...15000 ft (0.00...4572.00 m)

Ordering and shipping details

GTIN	731304286226
Package weight(Lbs)	11.46 lb(US) (5.2 kg)

Packing Units

Package 1 Height	5.00 in (12.7 cm)
Package 1 width	17.48 in (44.4 cm)
Package 1 Length	15.98 in (40.6 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------