



### Overview

Lead time	Usually in Stock
-----------	------------------

### Physical

Color	Black
Depth	27.56 in (70 cm)
Height	6.26 in (15.9 cm)
Product Weight	50.04 lb(US) (22.7 kg)
Width	4.21 in (10.7 cm)

### Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...3333 ft
Ambient Air Temperature for Storage	32...104 °F (0...40 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...15000 ft (0.00...4572.00 m)

### Ordering and shipping details

GTIN	00731304123538
Package weight(Lbs)	52.91 lb(US) (24 kg)

### Packing Units

Package 1 Height	7.09 in (18 cm)
Package 1 width	5.91 in (15 cm)
Package 1 Length	31.89 in (81 cm)
SCC14	20731304123532
Number of Units in Package 3	32

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Take-back	Take-back program available