

Product data sheet

Specifications

APC



APC NetShelter SV, Server Rack Enclosure, 42U, Black, 2057H x 800W x 1060D mm, with Roof, Castors, Feet, 4 Brackets, Bottom and Side Panels

AR2480

Overview

Presentation

Wide Universal IT enclosure with increased cable management options for denser server and networking applications. Includes integrated vertical 1U mounting spaces adjacent the enclosures standard EIA-310 equipment mounting u-spaces that can be removed and replaced with 1U accessories. 42U height to easily roll through doorways.

Lead time

Usually in Stock

Main

Product or Component Type	Rack enclosure
Number of rack unit	42U
Provided equipment	Baying hardware Doors Key(s) Keyed-alike doors and side panels Leveling feet Mounting Hardware Pre-installed casters 4 x Bolt down brackets Roof Side Panels Unpacking sheet

Physical

Height	80.98 in (205.7 cm)
Width	31.50 in (80 cm)
Depth	41.73 in (106 cm)
Product Weight	287.7 lb(US) (130.5 kg)
Color	Black
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	30.60 in (77.72 cm)
Minimum Mounting Depth	6.60 in (16.76 cm)
Rack Width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 18 gauge post 16 gauge rear door 19 gauge roof 18 gauge side panels
Permanent permissible load	1014 lb(US) (459.9 kg) dynamic 2205 lb(US) (1000.2 kg) static

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
GTIN	731304302070
Returnability	No
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	85.87 in (218.1 cm)
Package 1 Width	37.01 in (94 cm)
Package 1 Length	45.67 in (116 cm)
Package weight(Lbs)	330.440 lb(US) (149.885 kg)

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle)	455
--	-----

Use Better

Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACH Regulation	REACH Declaration

Use Again

Repack and remanufacture

Circularity Profile	End of Life Information
Take-back	No

Image of product / Alternate images

Alternative















