

Product data sheet

Specifications



license, Ecostruxure Machine Expert, professional, node locked, single, 1 user

ESECAPCZZSPAZZ

Main

Range of product	EcoStruxure Machine Expert
Product or component type	License
Format	Digital
Software type	Professional
Type of license	Node locked license
Software version	V2.2
Operating system requirement	Windows 10 64 bit Windows 11 64 bit
User language	English Spanish Chinese French German Italian Portuguese (Brazilian) Turkish Japanese

Complementary

License category	Permanent
Software function	Engineering Programming PLC

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Range compatibility	Modicon M241
	Modicon M251
	Modicon M262
	Modicon TM3
	Modicon TM5
	Modicon TM7
	PacDrive LMC Eco
	PacDrive LMC Pro
	PacDrive LMC Pro2
	Preventa XPSMC
	Preventa XPSMCM
	Lexium 32
	Lexium 32i
	Lexium 32M
	Lexium 52
	Lexium 62
	Lexium ILA
	Lexium ILE
	Lexium ILS
	Lexium SD3
	Altivar 320
	Altivar 340
	Altivar Process ATV600
	Altivar Easy 610
	Altivar 660 Drive System
	Altivar Process ATV900
	Altivar Process 980 Regenerative Drive System
	Harmony XB5R
	Harmony XB4R
	OsiSense XG
	OsiSense XUW
	TeSys U
	TeSys T
	TeSys island
	Magelis XBT GH
	Magelis GTO
	Magelis GTU
	Magelis GTUX
	Magelis iPC
	Magelis STO & STU
	Magelis GK
	Magelis SCU
	EcoStruxure Machine Expert Twin
Communication port protocol	Modbus SL
	Modbus TCP
	EtherNet/IP
	CANopen
	Sercos III
	CANmotion
Hosting option	On-premise
License size	Single (1 user)
System requirements	8 GB RAM
	15 GB hard disk space
Processor requirement	Intel Core 2 Duo
Display resolution	1280 x 1024 pixels

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.1 cm
Package 1 Width	0.1 cm
Package 1 Length	0.1 cm
Package 1 Weight	0.001 kg