

Product data sheet

Specifications



Illuminated push button, Harmony 9001K, metal, mushroom 41mm, green, 30mm, 2 positions, push pull, 110...120V, 1 CO

9001KR9P1GH13

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range of Product	Harmony 9001K
Product or Component Type	Illuminated push-button
Device short name	K
Type of operator	push-pull
Operator profile	Green mushroom Ø 41 mm
Operator additional information	Screw-on plastic

Complementary

Bezel material	Metal
Mounting diameter	1.2 in (30 mm)
Light source	incandescent
Light source	Incandescent bulb
Bulb base	BA 9s
Light block supply	Via integral transformer
[Us] rated supply voltage	110...120 V AC
Contacts type and composition	1 C/O
Connections - terminals	Screw clamp terminals
Operating position	Any position
[Ie] rated operational current	10 A, AC-15 10 A, DC-13
Contact operation	Standard
Device presentation	Complete product
Cap/operator or lens colour	Green
[Us] rated supply voltage	110...120 V
Light block supply	Via integral transformer
Operator profile	Mushroom Ø 41 mm
Type of operator	Push-pull
Operator position information	2 positions
Supply frequency	50...60 Hz
Size	30 mm

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

Product Certifications	CE UL listed file E42259 CCN NKCR CSA LR 25490 class 3211 03 NEMA
------------------------	--

NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13
---------------------------	-------------------------

Ordering and shipping details

Category	US10CS121426
----------	--------------

Discount Schedule	0CS1
-------------------	------

GTIN	785901034155
------	--------------

Returnability	No
---------------	----

Country of origin	MX
-------------------	----

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Nbr. of units in pkg.	1
-----------------------	---

Package 1 Height	11.43 in (29.032 cm)
------------------	----------------------

Package 1 Width	4.50 in (11.43 cm)
-----------------	--------------------

Package 1 Length	29.03 in (73.742 cm)
------------------	----------------------

Package weight(Lbs)	9.44 oz (267.62 g)
---------------------	--------------------

Contractual warranty

Warranty	18 months
----------	-----------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	Ae0c4eb9-0bfb-40a4-851f-5c619fbe777d
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture

Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.