

# Product data sheet

Specifications



variable speed drive, SFlex Altivar  
212, 460V AC, 3 phase, 7.5hp,  
enclosed drive

SFD212GG4YB07D07

Product availability: Stock - Normally stocked in distribution facility

## Main

Product or Component Type Variable speed drive

Motor power kW 5.5 kW

Maximum Horse Power Rating 7.5 hp

Nominal output current 11 A 460 V

## Ordering and shipping details

Category US1CP4D22199

Discount Schedule CP4D

GTIN 785901001607

Returnability Yes

Country of origin MX

## Packing Units

Unit Type of Package 1 PCE

Nbr. of units in pkg. 1

Package 1 Height 21.69 in (55.1 cm)

Package 1 Width 22.01 in (55.9 cm)

Package 1 Length 47.99 in (121.9 cm)

Package weight(Lbs) 94.0008 lb(US) (42.638 kg)

## Contractual warranty

Warranty 18 months

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Use Better

#### Materials and Substances

Packaging made with recycled cardboard	No
--	----

Packaging without single use plastic	No
--------------------------------------	----

### Use Again

#### Repack and remanufacture

Take-back	No
-----------	----