

Product data sheet

Specifications



APC NetShelter Power Cord, Locking, IEC C19 to NEMA 5-15P, 3.0m

AP8750

Overview

Presentation	Free up space and secure power cords between rack-mount PDUs and attached IT equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads.
---------------------	---

Lead time	Usually in Stock
------------------	------------------

Main

Product or component type	Power cord
Main Output Voltage	120 V
Input Connection Type	NEMA 5-15P
Cable length	3.00 m
Number of cables	1

Physical

Colour	Black
Height	23 cm
Width	23 cm
Depth	4.5 cm
Product weight	0.51 kg
Mounting preference	No preference
Mounting mode	Not rack-mountable

Input

Max line current	15 A
Input current limits	15 A

Output

Max current draw	15 A
Number of power socket outlets	1 IEC 60320 C19
Power cable length	3.05 m

Conformance

Product certifications	CSA PSE UL listed
-------------------------------	-------------------------

Environmental

Ambient air temperature for operation	0...105 °C
Relative humidity	20...80 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...105 °C
Storage Relative Humidity	20...80 %
Storage altitude	0...15240 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	23 cm
Package 1 Width	4.5 cm
Package 1 Length	23 cm
Package 1 Weight	0.51 kg
SCC14	10731304279737

Contractual warranty

Warranty	2 years repair or replace
-----------------	---------------------------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant
SCIP Number	1cdb2fed-a06f-4574-913d-8df8e70936b2
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
Halogen-free status	Product contains halogen above thresholds

Use Again

Repack and remanufacture

End of life manual availability	End of Life Information
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins