

Product data sheet

Specifications



Mounting plate, Linergy HK, 3P, 25A, 4.4mm², 190x54x61mm

AK5PA232S

Main

Range	Linergy
Product name	HK
Product or component type	Mounting plate
Poles description	3P
[I _{th}] conventional free air thermal current	25 A
I ² t on activation	200000 A ² .s
Number of cables	3 cable(s) 4 mm ² at 105 °C
Width	106 mm
Height	190 mm
Depth	63 mm

Complementary

[U _i] rated insulation voltage	690 V conforming to IEC 60439-1
9 mm pitches	12
Net weight	0.61 kg

Environment

Standards	IEC 60439
Product certifications	CSA LROS (Lloyds register of shipping) UL DNV

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.300 cm
Package 1 Width	12.500 cm
Package 1 Length	20.500 cm
Package 1 Weight	814.900 g
Unit Type of Package 2	S03
Number of Units in Package 2	9
Package 2 Height	30.000 cm

Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	8.048 kg

Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant
California proposition 65	<p>WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov</p>

Use Again

Repack and remanufacture

Take-back	No
WEEE Label	<p> The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins</p>